



The NEW Synea Fusion: A synthesis of design, technology and value

**NEW**

The new range of Synea Fusion handpieces from W&H builds on the long established and respected reputation of the W&H Synea brand. Synea Fusion offers a practical range of quality handpieces at an exceptionally attractive price.

Love handpieces? Love Synea Fusion.

synea FUSION



Type:	TG-98 L / TG-97 L / TG-97	TG-98 LM / TG-97 LM	TG-98 L RM / TG-97 L RM /	TG-98 L N / TG-97 L N /
Light:	LED + / no	compact glass rod	LED +	compact glass rod
Coupling:	Roto Quick	Multiflex®*	RM-connection	NSK Mach®**
Head size (Ø):	11.5 / 10.0	11.5 / 10.0	11.5 / 10.0	11.5 / 10.0
Power (W):	19 / 16	19 / 16	19 / 16	19 / 16
Speed (rpm):	360,000 / 390,000	360,000 / 390,000	360,000 / 390,000	360,000 / 390,000
Max. length of rotating instruments (mm):	25 / 21	25 / 21	25 / 21	25 / 21
Operating pressure (bar):	3±0.3	2.5 – 4	3±0.3	3±0.3
Spray:	4-hole	4-hole	4-hole	4-hole

* Multiflex® is a trademark of a third party not affiliated with W&H Dentalwerk Bürmoos GmbH

** NSK Mach® is a registered trade mark of NSK NAKANISHI INC., Japan



Type:	WG-99 LT / WG-99 A	WG-66 LT / WG-66 A	WG-56 LT / WG-56 A	HG-43 A
Light:	halogen / no	halogen / no	halogen / no	no
Head size (Ø):	9.5	9.5	9.5	–
Transmission/reduction:	1:5	2:1	1:1	1:1
Maximum motor speed (rpm):	40,000	40,000	40,000	40,000
Rotating instruments:	FG-burs	contra-angle burs	contra-angle burs	handpiece and contra-angle burs
Motor coupling:	ISO 3964	ISO 3964	ISO 3964	ISO 3964
Spray:	4-hole (> 50ml/min)	1-hole (> 50ml/min)	1-hole (> 50ml/min)	1-hole (> 50ml/min)
Intensity of illumination (light versions):	25,000 lux	25,000 lux	25,000 lux	–

Pictures are for illustrative purposes only. Additional equipment and accessories shown are not included as standard.

W&H Dentalwerk Bürmoos GmbH
 Ignaz-Glaser-Straße 53, Postfach 1
 5111 Bürmoos, Austria
 t +43 6274 6236-0
 f +43 6274 6236-55
 office@wh.com
 wh.com

20385 AEN Rev. 003 / 27.07.2015
 Subject to alterations